





UNI EN ISO 9001:2015 UNI EN ISO 14001:2015 UNI ISO 45001:2018

Antiox AHM/FF2

OBSOLETE

Description

ANTIOX AHM/FF2 is a synergistic blend of five non staining antioxidants, including three primary phenolic stabilizers, a thio-ester for the long term stability, and finally a phosphite, for the high temperature protection. Its physical form avoids dust formation and it has good flowing properties.

Application

This formula is specially designed for a wide spectrum protection either of hot-melt polymer systems or of polymer solutions. It can be used with adhesives, pressure sensitive adhesives, coatings, injection moulding or extrusions.

Technical Specifications

%	
99±1	
°C	
85 - 100	
	99±1 ℃

Handling

1) For HOT-MELT adhesives ANTIOX AHM/FF2 is very efficient at the following concentrations : a) Thermoplastic rubbers, like SIS, SBS (e.g. Cariflex, Solprene, etc.): 1.2 - 1.5% on rubber content.

b) Ethylene-vinylacetate (EVA, type ELVAX, etc.):
0.3 - 0.5% on EVA content.
c) Thermoplastic polyurethanes (e.g. ESTANE, DESMOCOLL, etc.):
0.2 - 0.4% on PU content.

d) Polyamides (e.g. Reammide, Versamide, etc.): 0.5 - 1.0% on PA content.

2) For SOLVENT BASED adhesives ANTIOX AHM/FF2 is very efficient at the following

concentrations : a) Natural rubber, SBR, chloroprene rubber, polvisoprene, butyl rubber: 0.25 - 0.5% on c

polyisoprene, butyl rubber: 0.25 - 0.5% on dry content.

ANTIOX AHM/FF2 can be introduced directly into the compound, together with other recipe ingredients, or predispersed into one of them or dissolved (if it is a matter of solvent). In the hot-melt continuos system (by extrusion process) it is advisable that a liquid component (like liquid rosin esters or naphtenic oil, etc.) is used to give some tack to the surface of granules, in order to have a fair distribution over the total mass. In the solvent systems, one can make a solution concentrate (exane, toluene, etc.), for example at 5 - 10% of solids.

Packaging

ANTIOX AHM/FF2 is normally supplied in 40-50 kg fibre drums.

Storing

ANTIOX AHM/FF2 must be stored in a dry place to avoid agglomeration. Shelf life is 1 year.

Mod. DT0104E - Antiox AHM/FF2 Creation date: 9 Jul 2002 Revision: 1 Revision date: 23 Jun 2006

1/1

Above information is reliable, but does not constitute warranty.